

Product data sheet

Characteristics

LAL36400MB

Circuit breaker, LA, 400A, 3 pole, 600VAC, 22kA, 250VDC, 10kA, lugs, thermal magnetic, short handle



Product availability: Stock - Normally stocked in distribution facility

Price*: 4619.00 USD



Main

Product or Component Type	Circuit breaker
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	400 A
Poles description	3P
Mounting Mode	Unit mount
Magnetic hold current	2000 A
Magnetic tripping current	4000 A
Operator profile	Short lever
Electrical connection	Lugs, load Lugs, line
Terminal identifier	AL400LA
Tightening torque	115.06 Lbf.In (13 N.m) 0.07...0.5 in ² (42...304 mm ²) (AWG 1...600 kcmil) 115.06 Lbf.In (13 N.m) 0.07...0.2 in ² (42...127 mm ²) (AWG 1...250 kcmil)
Height	11 In (279.4 mm)
Width	6 In (152.4 mm)
Depth	5.84 In (148.34 mm)
Circuit breaker application	HACR rated

Environment

Product Certifications	CSA[RETURN]IEC[RETURN]JUL Listed
------------------------	----------------------------------

Ordering and shipping details

Category	US10DE200935
Discount Schedule	0DE2
GTIN	785901005513
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.40 In (28.956 cm)
Package 1 Width	11.90 In (30.226 cm)
Package 1 Length	16.90 In (42.926 cm)
Package 1 Weight	16.162 Lb(US) (7.331 kg)

Environmental data

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
SCIP Number	45160aaa-1457-439f-bca7-7bd5246ac23e
California proposition 65	WARNING: This product can expose you to chemicals including: DIN-P, which is known to the State of California to cause cancer, and DID-P, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions EU RoHS Declaration
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**