

Product data sheet

Characteristics

MA4IMA161

Surge protection module, Surgelogic, MA, 160kA, 480Y/277VAC, 3 phase, 4 wire, SPD type 1



Product availability: Stock - Normally stocked in distribution facility

Price*: 675.00 USD



Main

Product or Component Type	Surge protection module
Range of Product	Surgelogic
Device short name	IMA
Accessory / separate part category	Replacement part

Complementary

[Ue] rated operational voltage	480Y/277 V AC
[Uc] maximum continuous operating voltage	320 V
Short-circuit protection	200 KA
Surge current	160 KA
Nominal Discharge Current	20 KA
Phase	3 phase
Wiring configuration	4-wire
Connections - terminals	Terminals
Local signalling	Status LED green normal operation
Provided equipment	Alarm enable/disable switch
Mounting Support	Panel mounting
Height	6.3 In (158.8 mm)
Width	3.3 In (82.8 mm)
Depth	2.7 In (68.3 mm)

Environment

NEMA Degree of Protection	NEMA 1
Enclosure material	Black Plastic
Standards	UL 1449:ed. 4 UL 1283:ed. 5 CSA C22.2 No 8:1986 ANSI/IEEE C62.41 ANSI/IEEE C62.45 NEC 285

Ordering and shipping details

Category	US1DE1B08467
Discount Schedule	DE1B
GTIN	785901075189
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.800 In (12.192 cm)
Package 1 Width	5.300 In (13.462 cm)
Package 1 Length	8.300 In (21.082 cm)
Package 1 Weight	31.567 Oz (894.937 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Product Life Status : **Commercialised**