



Main

Range	Acti 9
Range of product	Acti 9 iEM3000
Device short name	IEM3250
Product or component type	Energy meter

Complementary

Poles description	3P 3P + N 1P + N
Type of measurement	Active energy Current Voltage Active power
Device application	Sub billing Partial meter
Accuracy class	Class 0.5S active energy IEC 62053-22 Class 0.5S active energy IEC 61557-12 Class C active energy EN 50470-3
Input type	external CT 1 A or 5 A
Line Rated Current	5 A 1 A
Rated voltage	100...277 V 173...480 V
Network frequency	50 Hz 60 Hz
Technology type	Electronic
Display type	LCD display
Sampling rate	32 samples/cycle
Measurement current	1...32767000 mA

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum value measured	99999999 MWh
Communication port protocol	Modbus RTU 9.6, 19.2 and 38.4 kbauds even/odd or none 4000 V
Communication port support	Screw terminal block RS485
Local signalling	Green indicator light power ON Yellow flashing LED accuracy checking Yellow indicator light communications are active on the Modbus port (Modbus)
Number of inputs	0
Number of outputs	0
Mounting mode	Clip-on
Mounting support	DIN rail
Connections - terminals	Current circuit screw terminals 0.01 in ² (6 mm ²) Voltage circuit screw terminals 0.00 in ² (2.5 mm ²)
Overvoltage category	III
Standards	IEC 61557-12 IEC 62053-22 IEC 61036 IEC 62053-23 UL 61010-1 IEC 61010
Product certifications	CE IEC 61010 safety) CE EN 61557-12 power monitor) CE IEC 61326-1 EMC) CULus UL 61010 safety) CULus ANSI C12.20 sub-meter) EAC sub-meter) RCM NMI M 6-1 sub-meter) UL

Environment

IP degree of protection	Front panel IP40 IEC 60529 Body IP20 IEC 60529
Pollution degree	2
Relative humidity	5...95 % 122 °F (50 °C)
Ambient air temperature for operation	-13...131 °F (-25...55 °C) - IEC
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Operating altitude	< 6561.68 ft (2000 m)
Color	White
9 mm pitches	10
Width	3.54 in (90 mm)
Height	3.74 in (95 mm)
Depth	2.72 in (69 mm)

Ordering and shipping details

Category	09786 - SE ENTRY POWER METER
Discount Schedule	PL1
GTIN	00785901718758
Nbr. of units in pkg.	1
Package weight(Lbs)	0.77 lb(US) (0.35 kg)
Returnability	No
Country of origin	CN

Packing Units

Package 1 Height	3.46 in (8.800 cm)
Package 1 width	3.86 in (9.800 cm)
Package 1 Length	4.13 in (10.500 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------