

# AR5.8

## Ambient Compensated Bimetallic Thermal Unit Class 20

Product availability : Non-Stock - Not normally stocked in distribution facility



⚠ Discontinued

### Main

|                       |                                |
|-----------------------|--------------------------------|
| Range of product      | AR                             |
| Thermal overload type | Ambient compensated bimetallic |
| Motor tripping class  | 20                             |

### Ordering and shipping details

|                       |                       |
|-----------------------|-----------------------|
| Category              | 21781 - THERMAL UNITS |
| Discount Schedule     | CP1                   |
| GTIN                  | 00785901586487        |
| Nbr. of units in pkg. | 6                     |
| Package weight(Lbs)   | 0.04 lb(US) (0.02 kg) |
| Returnability         | No                    |
| Country of origin     | MX                    |

### Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 0.80 in (2.032 cm) |
| Package 1 width  | 2.30 in (5.842 cm) |
| Package 1 Length | 3.20 in (8.128 cm) |

### Offer Sustainability

|                           |   |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope  |
| China RoHS Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.  |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---