

D321NRB

Safety switch, general duty, fusible, 30A, 3 poles, 7.5 hp, 240 VAC, NEMA 3R, bolt-on provision, neutral factory installed

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Single Throw Safety Switch
Current Rating	30 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 3R
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Mounting Type	Surface
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	General duty
Voltage Rating	240 V AC
Wire Size	AWG 14...AWG 6 copper AWG 12...AWG 6 aluminium

Complementary

Maximum Horse Power Rating	1.5 hp 240 V AC 60 Hz 1 phase NEC 240.6 3 hp 240 V AC 60 Hz 3 phase NEC 240.6 3 hp 240 V AC 60 Hz 1 phase NEC 430.52 7.5 hp 240 V AC 60 Hz 3 phase NEC 430.52
Width	7.75 in (196.85 mm)
Height	9.63 in (244.60 mm)
Depth	3.75 in (95.25 mm)
Tightening torque	30 lbf.in (3.39 N.m) 0.00...0.02 in ² (2.08...13.3 mm ²) AWG 14...AWG 6)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00106 - D & DU SW,NEMA3R, 30-200A
Discount Schedule	DE1A
GTIN	00785901461067
Package weight(Lbs)	4.9 lb(US) (2.22 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 2 Weight	26.15 lb(US) (11.861 kg)
Package 3 Weight	676.00 lb(US) (306.628 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

