

DFCC2V

Fuse carrier TeSys DF, 2P 30A, fuse class CC, blown fuse indicator

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys DF
Product or component type	Fuse carrier
Device short name	DFCC
Poles description	2P
Fuse type	, CC
Control type	Toggle padlockable
Local signalling	Blown fuse indication
Utilisation category	AC-20B IEC 60947-3
[Ue] rated operational voltage	600 V AC
[Ie] rated operational current	30 A
[Ui] rated insulation voltage	600 V AC
[Uimp] rated impulse withstand voltage	6 kV
Short-circuit withstand	200 kA 600 V UL 512
Power dissipation in W	3 W maximum power dissipation by fuse

Complementary

Standards	UL 4248-1 UL 4248-4 CSA C22.2 No 4248-1 CSA C22.2 No 4248-4
Product certifications	UL Recognized CSA
Mounting support	35 mm symmetrical DIN rail
Mounting position	Vertical +/- 23°
Connections - terminals	screw clamp terminals 1 0.00...0.02 in ² (1...16 mm ²)rigid

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

screw clamp terminals 2 0.00...0.01 in² (1...6 mm²)rigid
 screw clamp terminals 1 0.00...0.02 in² (1...16 mm²)flexible with or without
 screw clamp terminals 2 0.00...0.01 in² (1...6 mm²)flexible with or without

Tightening torque	17.70 lbf.in (2 N.m) PZ2 17.70 lbf.in (2 N.m) flat Ø 5.5 mm
Height	3.13 in (79.5 mm)
Width	1.38 in (35 mm)
Depth	2.40 in (61 mm)
Net Weight	0.19 lb(US) (0.085 kg)
Quantity per set	Set of 6

Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-40...158 °F (-40...70 °C) with derating above 20°C
Operating altitude	0...6561.68 ft (0...2000 m) without derating
IP degree of protection	IP20
Pollution degree	3
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility code	DFCC

Ordering and shipping details

Category	21714 - DF FUSEHOLDERS
Discount Schedule	CP1
GTIN	00785901574569
Nbr. of units in pkg.	6
Package weight(Lbs)	0.26 lb(US) (0.12 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Package 1 Height	0.885 dm
Package 1 width	0.350 dm
Package 1 Length	0.645 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------