

Product data sheet

Characteristics

EZM1400TB

EZ meter, center main unit, 400 A, 1 PH, 3 wire, main lugs, N3R, busbar, AI

Product availability : Stock - Normally stocked in distribution facility



Main

Range of product	EZ meter-pak
Product or component type	Meter center main unit
Main type	Main Lugs
Included Items	Box

Complementary

Main rated current	400 A
Bus rated current	800 A
Material	Aluminium busbar
Enclosure material	Steel
[Ue] rated operational voltage	120/240 V AC
Device mounting	Surface
Number of Phases	1 phase in 1 phase out
Service feed location	UG OH
Electrical connection	Lugs 1 AWG 6...300 kcmil aluminium/copper) ground Lugs 2 AWG 3/0...500 kcmil aluminium/copper) line Lugs 2 AWG 3/0...500 kcmil aluminium/copper) neutral
Wiring configuration	3-wire
Height	30.46 in (773.68 mm)
Width	17.00 in (431.80 mm)
Depth	6.53 in (165.86 mm)

Environment

Product certifications	UL Listed
------------------------	-----------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Enclosure Rating	NEMA 3R
------------------	---------

Ordering and shipping details

Category	00020 - EZ METER-PAK
Discount Schedule	DE4
GTIN	00785901304852
Nbr. of units in pkg.	1
Package weight(Lbs)	43 lb(US) (19.50 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	8.20 in (20.828 cm)
Package 1 width	21.00 in (53.340 cm)
Package 1 Length	31.50 in (80.010 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------