

GS1DDU3

TeSys GS, disconnect switch, fuse, 3 P, 600 V,
UL 30 A, Type CC fuse

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS1 DD
Product or component type	Switch-disconnector-fuse
Device application	Protection
Design	Compact
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I _{th}] conventional free air thermal current	30 A 104 °F (40 °C)
[I _e] rated operational current	30 A
Fuse type	UL
Fuse size	CC
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Type of operating handle	External frontal Direct frontal
Mounting support	Rail Plate
[U _i] rated insulation voltage	690 V
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	15 kW 400 V 18.5 kW 500 V 25 kW 690 V
Short-circuit withstand	5.5 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - terminals	Power circuit lugs-ring terminals 0.00...0.01 in ² (2...6 mm ²)
Tightening torque	Power circuit 26.55 lbf.in (3 N.m)

Environment

Standards	UL98 CSA C22.2 No 4
Product certifications	LROS (Lloyds register of shipping) LOVAG ASEFA
IP degree of protection	IP20 IEC 60529 with terminal cover)
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) body IEC 60695-2-1
Height	4.57 in (116 mm)
Width	3.82 in (97 mm)
Depth	3.29 in (83.5 mm)
Net Weight	1.32 lb(US) (0.6 kg)

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901179535
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25 lb(US) (0.57 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.88 in (12.4 cm)
Package 1 width	7.09 in (18 cm)
Package 1 Length	5.67 in (14.4 cm)
Package 2 Weight	10.75 lb(US) (4.875 kg)
Package 3 Weight	119.50 lb(US) (54.204 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------