

Product availability : Stock - Normally stocked in distribution facility



Main

Range of product	Square D
Product or component type	Safety switch grounding bar
Series name	Heavy duty

Complementary

Line Rated Current	30 A F1 30 A F5 30 A F7 60 A F1 60 A F3 60 A F5 60 A F7
AWG gauge	AWG 12 copper AWG 10 aluminium AWG 4 copper or aluminium
Width	1.054 in (26.77 mm)
Height	0.437 in (11.10 mm)
Depth	0.312 in (7.92 mm)
Tightening torque	20 lbf.in (2.26 N.m) AWG 14...AWG 10) 20 lbf.in (2.26 N.m) AWG 12...AWG 10) 25 lbf.in (2.82 N.m) AWG 8) 35 lbf.in (3.95 N.m) AWG 6...AWG 4) 25 lbf.in (2.82 N.m) 2 x AWG 14...2 x AWG 10) 25 lbf.in (2.82 N.m) 2 x AWG 10...2 x AWG 10)

Ordering and shipping details

Category	00058 - MISC SWITCH ACCESSORIES
Discount Schedule	DE1

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	00785901421818
Nbr. of units in pkg.	10
Package weight(Lbs)	0.05 lb(US) (0.02 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.30 in (0.762 cm)
Package 1 width	0.60 in (1.524 cm)
Package 1 Length	1.10 in (2.794 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------