

Product availability : Stock - Normally stocked in distribution facility



Main

Range	I-Line
-------	--------

Complementary

Main Type	Universal Mains
Width	36.91 in (937.51 mm)
Height	66.03 in (1677.16 mm)
Depth	8.85 in (224.79 mm)
Product Destination	Panelboard interior HCR-U 44 in (1117.60 mm) 86 in (2184.40 mm)
Rated Current	1200 A
Mounting Space	108 in (2743.20 mm)
Net Weight	275.00 lb(US) (124.74 kg)

Ordering and shipping details

Category	00016 - I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901001355
Nbr. of units in pkg.	1
Package weight(Lbs)	215 lb(US) (97.52 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.81 ft (0.246 m)
Package 1 width	3.50 ft (1.067 m)
Package 1 Length	5.75 ft (1.753 m)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------