

Product data sheet

Characteristics

HJL36150M74

Motor circuit protector, PowerPacT H, unit mount, 150A, 3 pole, 25 kA, 600 VAC, 80% rated

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Motor Circuit Protector
---------------------------	-------------------------

Complementary

Number of Poles	3P
Breaking capacity code	J
[Ith] conventional free air thermal current	58...130 A
Magnetic tripping current	348...1690 A
Electrical connection	Lugs load Lugs line
Tightening torque	44.25 lbf.in (5 N.m) 0.00...0.15 in ² (2.5...95 mm ²) AWG 14...AWG 3/0
Height	6.4 in (162.56 mm)
Width	4.12 in (104.65 mm)
Depth	4.36 in (110.74 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01125 - HJ, JJ UNT MNT MTR CIRCUIT PROTECTR
Discount Schedule	DE2
GTIN	00785901486602
Nbr. of units in pkg.	1
Package weight(Lbs)	4.38 lb(US) (1.99 kg)
Returnability	Yes
Country of origin	MX

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Package 1 Height	5.80 in (14.732 cm)
Package 1 width	7.50 in (19.050 cm)
Package 1 Length	8.80 in (22.352 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

