

# Product data sheet

## Characteristics

# HOM2150

Mini circuit breaker, Homeline, 150A, 4 pole, 120/240 VAC, 10 kA AIR, standard type, plug in mount

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	150 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	4P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 4...300 kcmil aluminium/copper)1

### Complementary

Tightening torque	35.40 lbf.in (4.0 N.m) AWG 4...AWG 2/0)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

### Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	00151 - HOM MAIN BREAKERS
Discount Schedule	DE3D
GTIN	00785901065838
Nbr. of units in pkg.	1
Package weight(Lbs)	1.76 lb(US) (0.80 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	3.70 in (9.398 cm)
Package 1 width	3.30 in (8.382 cm)
Package 1 Length	4.20 in (10.668 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	Lifetime
----------	----------