

Product data sheet

Characteristics

HOM220GFI

Mini circuit breaker, Homeline, 20A, 2 pole, 120/240 VAC, 10 kA AIR, ground fault class A, plug in mount

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	AWG 12...AWG 4 aluminium) ¹ AWG 14...AWG 6 copper) ¹

Complementary

Tightening torque	40.71 lbf.in (4.6 N.m) 0.00...0.02 in ² (2.5...10 mm ²) AWG 16...AWG 14) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in ² (4...20 mm ²) AWG 12...AWG 4)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00147 - HOM 2 POLE GFI CB,40A MAX
Discount Schedule	DE3D
GTIN	00785901303206
Nbr. of units in pkg.	33
Package weight(Lbs)	33 lb(US) (14.97 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.40 in (8.636 cm)
Package 1 width	2.40 in (6.096 cm)
Package 1 Length	5.30 in (13.462 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	33
Package 2 Weight	39.06 lb(US) (17.717 kg)
Package 2 Height	5.40 in (13.716 cm)
Package 2 width	13.70 in (34.798 cm)
Package 2 Length	20.70 in (52.578 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Halogen content performance	Halogen free product

Contractual warranty

Warranty	Lifetime
----------	----------