

Product data sheet

Characteristics

HOMC30UC

Load center cover, Homeline, 30 spaces, combo flush and surface, gray

Product availability : Stock - Normally stocked in distribution facility



Main

Product Type	Load Center Cover
Marketing Trade Name	Homeline
Cover Type	Combination flush/surface cover

Complementary

Number of Spaces	30
Surface Finish	Baked enamel Gray
Height	34.98 in (888.49 mm)
Width	15.44 in (392.18 mm)
Tightening Torque	Screw 2.3 N.m

Ordering and shipping details

Category	00183 - HOM LC REPLACEMENT COVERS
Discount Schedule	DE5
GTIN	00785901077541
Nbr. of units in pkg.	1
Package weight(Lbs)	12.05 lb(US) (5.47 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	1.20 in (3.048 cm)
Package 1 width	15.70 in (39.878 cm)
Package 1 Length	35.40 in (89.916 cm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	Lifetime
----------	----------