

# HOMT1515240

Tandem mini circuit breaker, Homeline, 2 x 1 pole at 15A, 1 x 2 pole at 40A, 120/240 VAC, 10 kA AIR, plug in mount

Product availability : Stock - Normally stocked in distribution facility



## Main

|                              |  |
|------------------------------|--|
| Product                      | Miniature circuit-breaker  |
| Range                        | Homeline   |
| Current Rating               | 15 A<br>40 A   |
| Certifications               | UL Listed  |
| Voltage Rating               | 120/240 V AC   |
| Mounting Type                | Plug-in  |
| Number of Poles              | 2P<br>1P   |
| Short Circuit Current Rating | 10 kA  |
| Number of Spaces             | 2  |
| Circuit Breaker Type         | Quad tandem  |
| Ratings                      | HACR rated   |
| Electrical Connection        | Box lugs   |
| Wire Size                    | AWG 14...AWG 8 aluminium/copper)1<br>AWG 14...AWG 6 copper)1<br>AWG 12...AWG 6 aluminium)1 |

## Complementary

|                   |  |
|-------------------|--|
| Tightening torque | 40.71 lbf.in (4.6 N.m) 0.00...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) AWG 14...AWG 6)<br>40.71 lbf.in (4.6 N.m) 0.00...0.03 in <sup>2</sup> (2.5...20 mm <sup>2</sup> ) AWG 14...AWG 2) |
| Height            | 3.13 in (79.50 mm)   |
| Width             | 2 in (50.80 mm)  |
| Depth             | 2.98 in (75.69 mm)   |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

|                                       |                |
|---------------------------------------|----------------|
| Ambient air temperature for operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

## Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 00046 - HOM/T 15-30A 1P; 15-60A 2P |
| Discount Schedule     | DE3D                               |
| GTIN                  | 00785901377023                     |
| Nbr. of units in pkg. | 5                                  |
| Package weight(Lbs)   | 0.85 lb(US) (0.39 kg)              |
| Returnability         | Yes                                |
| Country of origin     | MX                                 |

## Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 2.00 in (5.080 cm) |
| Package 1 width  | 3.00 in (7.620 cm) |
| Package 1 Length | 3.20 in (8.128 cm) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|