

Product data sheet

Characteristics

HOMT215240

Quad tandem mini circuit breaker, Homeline, 1 x 2 pole at 15A, 1 x 2 pole at 40A, 120/240 VAC, 10 kA AIR, plug in mount

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A 40 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2.0
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 14...AWG 8 aluminium/copper)1 AWG 14...AWG 6 aluminium/copper)1

Complementary

Tightening torque	40.71 lbf.in (4.6 N.m) 0.00...0.02 in ² (2.5...10 mm ²) AWG 14...AWG 6) 40.71 lbf.in (4.6 N.m) 0.00...0.03 in ² (2.5...20 mm ²) AWG 14...AWG 2)
Height	3.13 in (79.50 mm)
Width	1.97 in (50.04 mm)
Depth	3.29 in (83.57 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901969679
Nbr. of units in pkg.	5
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	3.30 in (8.382 cm)
Package 1 width	2.00 in (5.080 cm)
Package 1 Length	3.30 in (8.382 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)