

Product data sheet

Characteristics

HOMT220230

Quad tandem mini circuit breaker, Homeline, 1 x 2 pole at 20A, 1 x 2 pole at 30A, 120/240 V, 10 kA AIR, plug in mount

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|------------------------------|-----------------------------------|
| Product | Miniature circuit-breaker |
| Range | Homeline |
| Current Rating | 20 A 30 A |
| Certifications | UL Listed |
| Voltage Rating | 120/240 V AC |
| Mounting Type | Plug-in |
| Number of Poles | 2P |
| Short Circuit Current Rating | 10 kA |
| Number of Spaces | 2.0 |
| Circuit Breaker Type | Quad tandem |
| Ratings | HACR rated |
| Electrical Connection | Box lugs |
| Wire Size | AWG 14...AWG 8 aluminium/copper)1 |

Complementary

| | |
|-------------------|---|
| Tightening torque | 35.40 lbf.in (4.0 N.m) 0.00...0.01 in ² (2.5...6 mm ²) AWG 14...AWG 8) |
| Height | 3.13 in (79.50 mm) |
| Width | 1.97 in (50.04 mm) |
| Depth | 3.23 in (82.04 mm) |

Environment

| | |
|---------------------------------------|----------------|
| Ambient air temperature for operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 00046 - HOM/T 15-30A 1P; 15-60A 2P |
| Discount Schedule | DE3D |
| GTIN | 00785901969754 |
| Nbr. of units in pkg. | 5 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|--------------------|
| Package 1 Height | 3.20 in (8.128 cm) |
| Package 1 width | 2.00 in (5.080 cm) |
| Package 1 Length | 3.30 in (8.382 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |