

# Product data sheet

## Characteristics

# HOMT230240

Quad tandem mini circuit breaker, Homeline, 1 x 2 pole at 30A, 1 x 2 pole at 40A, 120/240 VAC, 10 kA AIR, plug in mount

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A 40 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2.0
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 14...AWG 8 aluminium/copper)1 AWG 14...AWG 6 aluminium/copper)1

### Complementary

Tightening torque	35.40...40.71 lbf.in (4.0...4.6 N.m) 0.00...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) AWG 14...AWG 6) 35.40...40.71 lbf.in (4.0...4.6 N.m) 0.00...0.03 in <sup>2</sup> (2.5...20 mm <sup>2</sup> ) AWG 12...AWG 6)
Height	3.13 in (79.50 mm)
Width	1.97 in (50.04 mm)
Depth	3.29 in (83.57 mm)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901970460
Nbr. of units in pkg.	5
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	3.20 in (8.128 cm)
Package 1 width	2.00 in (5.080 cm)
Package 1 Length	3.30 in (8.382 cm)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)