

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LRD43.. LR3D15.. LR2D LRD33.. LR3D43.. LR3D35.. LRD15.. LR3D33..
[Uc] control circuit voltage	110 V AC 50/60 Hz 110 V DC

Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net Weight	0.20 lb(US) (0.09 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901055129
Nbr. of units in pkg.	1
Package weight(Lbs)	0.26 lb(US) (0.12 kg)
Returnability	Yes

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	FR
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.89 in (4.8 cm)
Package 1 width	1.89 in (4.8 cm)
Package 1 Length	1.97 in (5 cm)
Package 2 Weight	7.92 lb(US) (3.592 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------