

Product availability : Non-Stock - Not normally stocked in distribution facility



## Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LRD313...LRD365 LR3D313...LR3D365 LR3D01...D35 LRD01...35
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC

## Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net Weight	0.20 lb(US) (0.09 kg)

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901636199
Nbr. of units in pkg.	1
Package weight(Lbs)	0.24 lb(US) (0.11 kg)
Returnability	No
Country of origin	FR

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.85 in (4.7 cm)
Package 1 width	1.89 in (4.8 cm)
Package 1 Length	2.01 in (5.1 cm)
Package 2 Weight	8.10 lb(US) (3.676 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------