

LJA36400CU44X

Circuit breaker, PowerPact L, I-Line, Micrologic 6.3A, 400A, 100% rated, 3 pole, 25 kA, 600 VAC, phase ABC

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range of product	PowerPact L
Product or component type	Circuit breaker
Trip Unit Type	Electronic, ammeter, Micrologic 6.3 A, LSIG
Interrupt Code	J

Complementary

Line Rated Current	400 A
Number of Poles	3P
Interrupt Rating	100 kA 240 V AC 65 kA 480 V AC 25 kA 600 V AC
Voltage Rating	600 V AC
Continuous current rating	100 %
Protection technology	Current limiter
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
Terminal Type	AL600LS52K3
Wire Size	AWG 2/0...500 kcmil aluminium/copper)2
Tightening torque	442.54 lbf.in (50 N.m) 0.11...0.37 in ² (70...240 mm ²) AWG 2/0...500 kcmil)
I-Line Phase Connection	ABC
Height	14.7 in (373.38 mm)
Width	5.94 in (150.88 mm)
Depth	6.61 in (167.89 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product certifications	CSA 22-2 CCC IEC CE UL 489 NMX NEMA
------------------------	---

Ordering and shipping details

Category	01118 - L ELEC TRIP I-LINE BREAKER/SW
Discount Schedule	DE2
GTIN	00785901732532
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

