

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Device short name	LUA1
Product or component type	Auxiliary contact

Complementary

Auxiliary contact composition	1 NO + 1 NC
Signalling function	Fault signalling Indicating rotary knob in ready position
[Ue] rated operational voltage	<= 250 V AC <= 250 V DC
[Ui] rated insulation voltage	250 V CSA 250 V IEC 60947-5-1 250 V UL
[Ith] conventional free air thermal current	2.5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Net Weight	0.07 lb(US) (0.03 kg)
Connections - terminals	screw clamp terminals

Ordering and shipping details

Category	22399 - TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	00785901202462
Nbr. of units in pkg.	1
Package weight(Lbs)	0.05 lb(US) (0.02 kg)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country of origin	CZ

Packing Units

Package 1 Height	0.200 dm
Package 1 width	0.900 dm
Package 1 Length	1.200 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------