

# Product data sheet

## Characteristics

# NC26SHR

Enclosure Cover - NQNF - Type 1 - Surface - Hinged - 20x26in

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Surface cover
Color	Gray
Cover type	Surface cover
Type of front plate	Hinged

### Complementary

Material	Steel
Height	26 in (660.40 mm)
Width	20 in (508.00 mm)
Tightening torque	Cover 10...12 lb.in

### Environment

Enclosure Rating	NEMA 1
Product certifications	CULus

### Ordering and shipping details

Category	08352 - NF / NQ TRIMS RTA
Discount Schedule	PE1A
GTIN	00785901329275
Nbr. of units in pkg.	1
Package weight(Lbs)	14.5 lb(US) (6.58 kg)
Returnability	Yes
Country of origin	US

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Package 1 Height	1.90 in (4.826 cm)
Package 1 width	22.00 in (55.880 cm)
Package 1 Length	27.90 in (70.866 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------