

NF600SFBH

NF Panelboard Acc. Subfeed Breaker Kit 600A, H Frame

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Circuit Breaker Sub-Feed Lug
Provided equipment	Cover plate 1 Mounting plate 1 Bracket for support 2 Screw set 1 Rail extension 2 Rail splice 2 Lug 5 Cables 6 Closing plate 1
Circuit breaker type	H-frame

Complementary

Current Rating	600 A
Tightening torque	60.18...64.61 lbf.in (6.8...7.3 N.m)

Environment

Product certifications	CULus
------------------------	-------

Ordering and shipping details

Category	08338 - NF (& SHARED) RTI ACCESSORIES
Discount Schedule	PE1A
GTIN	00785901834649
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------