



## Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	15.75 in (400 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	9.84 in (250 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Solid
Mounting plate description	Without mounting plate

## Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body steel

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Surface finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product certifications	CUL UL
Net Weight	23.85 lb(US) (10.816 kg)

## Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262

## Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	00785901855446
Nbr. of units in pkg.	1
Package weight(Lbs)	23.5 lb(US) (10.66 kg)
Returnability	No
Country of origin	ES

## Packing Units

Package 1 Height	16.54 in (420.000 mm)
Package 1 width	24.41 in (620.000 mm)
Package 1 Length	10.63 in (270.000 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------