



Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	31.50 in (800 mm)
Enclosure nominal width	31.50 in (800 mm)
Enclosure nominal depth	7.87 in (200 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 door with lock 1 mounting plate 2 cable gland plate bottom
Door type	Solid
Mounting plate description	Plain

Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

	Mounting plate galvanised steel
Surface finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208
Product certifications	UL CUL
Net Weight	72.75 lb(US) (33 kg)

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	03606480211751
Nbr. of units in pkg.	1
Package weight(Lbs)	81.44 lb(US) (36.94 kg)
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	32.28 in (82 cm)
Package 1 width	32.28 in (82 cm)
Package 1 Length	8.66 in (22 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------