

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	Spacial
Product name	Spacial CRNG
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	47.24 in (1200 mm)
Enclosure nominal width	47.24 in (1200 mm)
Enclosure nominal depth	11.81 in (300 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 lock 2 cable gland plate bottom 2 door
Door type	Solid
Mounting plate description	Without mounting plate

Complementary

Body type	Single piece body
Number of doors	Front face 2
Door opening side	Reversible 120 °)
Lock type	3 points lock, 5 mm double-bar
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body steel

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Surface finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product certifications	CUL UL
Net Weight	142.42 lb(US) (64.6 kg)

Environment

IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	03606480298318
Nbr. of units in pkg.	1
Package weight(Lbs)	142.12 lb(US) (64.46 kg)
Returnability	No
Country of origin	FR

Packing Units

Package 1 Height	48.27 in (1226.000 mm)
Package 1 width	48.27 in (1226.000 mm)
Package 1 Length	12.99 in (330.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------