

# Product data sheet

## Characteristics

# NSYS3X10830

SPACIAL S3X stainless 304L, Scotch Brite® finish, H1000xW800xD300 mm.

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	39.37 in (1000 mm)
Nominal width	31.50 in (800 mm)
Nominal depth	11.81 in (300 mm)
Product installation	Wall-mounting
Device composition	1 body 1 reinforcement frame drilled door 1 door 2 lock door

### Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Solid
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

	Hinge stainless steel
Surface finish	Body and door Scotch-Brite® brushed Lock chromium plated
Net Weight	82.45 lb(US) (37.4 kg)

## Environment

Standards	IEC 62208
Product certifications	UL 508 type A CAN/CSA 22
IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Environmental characteristic	Corrosive Specific hygiene

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901617587
Nbr. of units in pkg.	1
Package weight(Lbs)	81.4 lb(US) (36.92 kg)
Returnability	Yes
Country of origin	BG

## Packing Units

Package 1 Height	40.16 in (1020.000 mm)
Package 1 width	12.80 in (325.000 mm)
Package 1 Length	32.09 in (815.000 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------