

Product data sheet

Characteristics

NSYTRAABV35

Lineryg terminal blocks, end bracket, screw on,
for 35 mm DIN rail, 9.5 mm wide, markable

Product availability : Stock - Normally stocked in distribution facility



Main

Range	Lineryg
Product name	TR
Product or component type	End stop
Device short name	TRA
Accessory / separate part category	Mounting accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Length	1.99 in (50.5 mm)
Thickness	0.37 in (9.5 mm)

Complementary

Mounting mode	By screws
Quantity per set	Set of 50
Net Weight	0.52 oz (14.8 g)
Color	Grey

Ordering and shipping details

Category	21715 - IEC TERMINAL BLOCKS-NSY,AM1,DF6,GK1
Discount Schedule	CP5
GTIN	00785901133704
Nbr. of units in pkg.	50
Package weight(Lbs)	0.03 lb(US) (0.01 kg)
Returnability	Yes

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	DE
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.30 in (3.3 cm)
Package 1 width	0.35 in (0.9 cm)
Package 1 Length	1.89 in (4.8 cm)
Package 2 Weight	26.60 oz (754 g)
Package 3 Weight	39.80 lb(US) (18.055 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------