

NSYTRAL42

PLUG-IN BRIDGE, 2POINTS FOR 4MM² TERMINAL BLOCKS, RED

Product availability : Stock - Normally stocked in distribution facility



Main

Range	Linergy
Product name	Linergy TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number of ways	2 ways

Complementary

Cable cross section	0.01 in ² (4 mm ²)
Number of connections	4 3 2
Number of measurement input	3 2 6 1 4
Quantity per set	Set of 10
Net Weight	0.07 oz (2 g)
Color	Red

Ordering and shipping details

Category	21715 - IEC TERMINAL BLOCKS-NSY,AM1,DF6,GK1
----------	---

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	CP5
GTIN	00785901447283
Nbr. of units in pkg.	50
Package weight(Lbs)	0.01 lb(US) (0.00 kg)
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.97 in (5 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	6.69 in (17 cm)
Package 2 Weight	3.53 oz (100 g)
Package 3 Weight	3.53 oz (100 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------