



Main

Product or Component Type	Circuit breaker
Range	PowerPact P
Current Sensor Rating Range	1200 A
Rated Current	1200 A
Breaking Capacity	100 kA 240 V AC 65 kA 480 V AC 25 kA at 600 V AC
AWG Gauge	AWG 3/0...500 kcmil aluminium/copper)4
Trip Unit Technology	Electronic, ammeter, Micrologic 3.0 A, LI

Complementary

Certifications	CSA UL Listed IEC
Rated operational Voltage	600 V AC
Module Type	P-Frame
Mounting Location	Bolt-on
Mounting Mode	Unit mount
Poles Description	3P
Circuit Breaker Rating Code	J
Electrical Connection	Lugs load Lugs line
Continuous Current Rating	100 %
Device Short Name	A
Height	16.16 in (410.46 mm)
Depth	8.05 in (204.47 mm)
Width	8.27 in (210.06 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Tightening Torque	442.54 lbf.in (50 N.m) 0.15...0.37 in ² (95...240 mm ²) AWG 3/0...500 kcmil) 8.85...11.51 lbf.in (1.0...1.3 N.m)
-------------------	--

Ordering and shipping details

Category	01215-PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Package weight(Lbs)	32.00 lb(US) (14.515 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------