

PK18GTA

Load center accessory, QO/Homeline, ground bar kit, 18 terminals

Product availability : Stock - Normally stocked in distribution facility



Main

Product line	QO
Product type	Load Center Grounding Bar Assembly

Complementary

Number of connectors	18
Wire size	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium
Provided equipment	2 screw
Bar length	6.57 in (167 mm)
Maximum length of segment	3.15 in (80 mm)
Device mounting	Direct mounting back of enclosure
Tightening torque	30 lb.in Mounting screw 30 lb.in : 20 lb.in, AWG 14...AWG 10, copper 20 lb.in, AWG 12...AWG 10, aluminium 35 lb.in, AWG 6...AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14...AWG 12, copper 25 lb.in, AWG 12...AWG 10, aluminium

Ordering and shipping details

Category	00102 - QO LC ACCESSORIES
Discount Schedule	DE3A
GTIN	00785901026426
Nbr. of units in pkg.	10
Package weight(Lbs)	0.25 lb(US) (0.11 kg)
Returnability	Yes

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	US
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.00 in (17.78 cm)
Package 1 width	3.50 in (8.89 cm)
Package 1 Length	0.40 in (1.016 cm)
Package 2 Weight	31.20 oz (884.504 g)
Package 3 Weight	465.00 lb(US) (210.92 kg)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

