

Product data sheet

Characteristics

PK23GTAL

Load center accessory, QO/Homeline, ground bar kit, 23 terminals, with AWG 1-4/0 lug in aluminum or copper

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|--------------|---------------------------|
| Product line | QO |
| Product type | Load Center Grounding Bar |

Complementary

| | |
|---------------------------|---|
| Number of connectors | 24 |
| Wire size | AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium AWG 4...AWG 1 aluminium/copper |
| Provided equipment | 2 screw |
| Bar length | 9.45 in (240 mm) |
| Maximum length of segment | 3.15 in (80 mm) |
| Device mounting | Direct mounting back of enclosure |
| Tightening torque | 30 lb.in Mounting screw 30 lb.in : 20 lb.in, AWG 14...AWG 10, copper 20 lb.in, AWG 12...AWG 10, aluminium 35 lb.in, AWG 6...AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14...AWG 12, copper 25 lb.in, AWG 12...AWG 10, aluminium |

Ordering and shipping details

| | |
|---------------------|---------------------------|
| Category | 00102 - QO LC ACCESSORIES |
| Discount Schedule | DE3A |
| GTIN | 00785901440895 |
| Package weight(Lbs) | 0.4 lb(US) (0.18 kg) |

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------|-----|
| Returnability | Yes |
| Country of origin | US |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions

