



Main

Device short name	A
Product or component type	Circuit breaker

Complementary

Line Rated Current	1000 A
Number of Poles	3P
Breaking capacity code	K
Electrical connection	I-Line connection line Lugs load
Tightening torque	442.54 lbf.in (50 N.m) 0.15...0.37 in ² (95...240 mm ²) AWG 3/0...500 kcmil) 8.85...11.51 lbf.in (1.0...1.3 N.m)
Height	16.16 in (410.46 mm)
Width	8.27 in (210.06 mm)
Depth	8.05 in (204.47 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01210-PG,H,J,K,L,N I-LINE BREAKERS
Discount Schedule	DE2
Package weight(Lbs)	32.00 lb(US) (14.515 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------