

Product data sheet

Characteristics

PKOGTA2

Grounding kit, Heavy Duty safety switch,
400-600A, Series E4-E5

Product availability : Stock - Normally stocked in distribution facility



Main

Range of product	Square D
Product or component type	Safety switch grounding bar
Series name	Heavy duty

Complementary

Line Rated Current	200 A F5 200 A F7
AWG gauge	AWG 2/0 copper or aluminium
Tightening torque	200 lbf.in (22.60 N.m) AWG 10...AWG 2/0 200 lbf.in (22.60 N.m) AWG 6...AWG 2/0

Ordering and shipping details

Category	00058 - MISC SWITCH ACCESSORIES
Discount Schedule	DE1
GTIN	00785901432678
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14 lb(US) (0.06 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.80 in (2.032 cm)
Package 1 width	1.60 in (4.064 cm)
Package 1 Length	2.00 in (5.080 cm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------