

Product data sheet

Characteristics

QBL32000S22LW

PowerPact Q - automatic molded case switch - 3-pole - 10 kA - 240 V - 225 A

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Automatic switch
Range of product	PowerPact Q
Trip unit technology	Magnetic
Provided equipment	Control cable ON and OFF end

Complementary

Line Rated Current	225 A
[Ue] rated operational voltage	240 V AC
Number of poles	3
Breaking capacity	10 kA 240 V AC
Breaking capacity code	B
Mounting mode	Unit mount
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper Lugs line AWG 4...300 kcmil aluminium/copper
Magnetic tripping current	4500 A
Height	6.47 in (164.34 mm)
Width	4.5 in (114.30 mm)
Depth	3.93 in (99.82 mm)
Tightening torque	247.82 lbf.in (28 N.m) 0.04...0.23 in ² (25...150 mm ²) AWG 4...300 kcmil)

Environment

Product certifications	CSA UL Listed
------------------------	------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00023 - QO,Q2L 3P ENCL & BREAKERS
Discount Schedule	DE2
GTIN	00785901874126
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------