

Product data sheet

Characteristics

QBM22150TN

PowerPact Q - molded case circuit breaker - 2-pole - 10 kA - 240 V - 150 A

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Line Rated Current	150 A
Breaking capacity code	B
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Tightening torque	247.82 lbf.in (28 N.m) 0.04...0.23 in ² (25...150 mm ²) AWG 4...300 kcmil)
Height	6.47 in (164.34 mm)
Width	4.5 in (114.30 mm)
Depth	3.93 in (99.82 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	00187 - Q2M REPL MAIN CB
Discount Schedule	DE2A
GTIN	00785901417873
Nbr. of units in pkg.	1
Package weight(Lbs)	3.27 lb(US) (1.48 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	4.50 in (11.430 cm)
------------------	---------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 width	6.10 in (15.494 cm)
Package 1 Length	9.80 in (24.892 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------