

Product data sheet

Characteristics

QO115PCAFI

Mini circuit breaker, QO, 15A, 1 pole, 120 VAC, 10 kA, combo arc fault, plug on neutral, plug in mount

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	PoN combination ARC-fault
Electrical Connection	Pressure plate
Connections Terminals	Plug-on neutral

Complementary

Interrupt Rating	10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Height	4.75 in (120.65 mm)
Width	0.75 in (19.05 mm)
Depth	2.91 in (73.91 mm)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	06303 - QO SINGLE POLE ARC FAULT CIRCUIT BREAKER
Discount Schedule	DE2A
GTIN	00785901062615
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 lb(US) (0.23 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.00 in (2.54 cm)
Package 1 width	3.80 in (9.652 cm)
Package 1 Length	4.90 in (12.446 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	52
Package 2 Weight	26.60 lb(US) (12.066 kg)
Package 2 Height	3.80 in (9.652 cm)
Package 2 width	13.90 in (35.306 cm)
Package 2 Length	20.80 in (52.832 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------