

Product data sheet

Characteristics

QO2030

Tandem mini circuit breaker, QO, 1 x 1 pole at 20A, 1 x 1 pole at 30A, 120/240 VAC, 10 kA, plug in mount

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|-----------------------|---------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Current Rating | 30 A 20 A |
| Voltage Rating | 120/240 V AC |
| Mounting Type | Plug-in |
| Number of Poles | 1P |
| Circuit Breaker Type | Tandem |
| Ratings | HACR rated |
| Electrical Connection | Box lugs |

Complementary

| | |
|------------------------|------------------------------------|
| Interrupt Rating | 10 kA 120/240 V AC 50/60 Hz |
| Number of Panel Spaces | 1 |
| Wire Size | AWG 14...AWG 8 copper or aluminium |
| Tightening Torque | 40.71 lbf.in (4.6 N.m) |
| Height | 3.22 in (81.79 mm) |
| Width | 0.75 in (19.05 mm) |
| Depth | 2.91 in (73.91 mm) |

Environment

| | |
|----------------|------------------|
| Certifications | UL Listed CSA |
| Ambient Rating | 104 °F (40 °C) |

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 00181 - REPLCMNT TANDEMS - DO NOT NEGOTIATE |
| Discount Schedule | DE2A |
| GTIN | 00785901001010 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.33 lb(US) (0.15 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|--------------------|
| Package 1 Height | 0.80 in (2.032 cm) |
| Package 1 width | 3.50 in (8.890 cm) |
| Package 1 Length | 3.50 in (8.890 cm) |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|