

# Product data sheet

## Characteristics

# QO220PL5392

Mini circuit breaker, QO, 20A, 2 pole, 120/240 VAC, 10 kA, Powerlink, plug in mount, 48 in leads

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Circuit breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	2
Provided Equipment	48 in (1219.20 mm) lead
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.55 in (115.57 mm)
Depth	2.91 in (73.91 mm)
Width	1.5 in (38.10 mm)

### Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	09650 - POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A
GTIN	00785901084143
Package weight(Lbs)	0.91 lb(US) (0.41 kg)
Returnability	Yes
Country of origin	MX

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------