

Product data sheet

Characteristics

QO230PL5392

Mini circuit breaker, QO, 30A, 2 pole, 120/240 VAC, 10 kA, Powerlink, plug in mount, 48 in leads

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Circuit breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	2
Provided Equipment	48 in (1219.20 mm) lead
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.55 in (115.57 mm)
Width	1.5 in (38.10 mm)
Depth	2.91 in (73.91 mm)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	09650 - POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A
GTIN	00785901741954
Nbr. of units in pkg.	1
Package weight(Lbs)	0.91 lb(US) (0.41 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	2.40 in (6.096 cm)
Package 1 width	3.50 in (8.890 cm)
Package 1 Length	5.30 in (13.462 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------