

Product availability : Stock - Normally stocked in distribution facility



Main

Marketing Trade Name	QO
Product	Load Center
Cover Type	Surface cover

Complementary

Tightening Torque	Main lugs 35 lb.in, AWG 14...AWG 10, aluminium/copper Main lugs 45 lb.in, AWG 3, aluminium/copper Main lugs 40 lb.in, AWG 8...AWG 4, aluminium/copper Main lugs 35 lb.in, AWG 12...AWG10, aluminium/copper
Load Center Type	Main lugs
Rated Current	70 A
Number of Spaces	2
Max Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	4
Maximum Number of Tandem Breakers	2
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 12...AWG 3 aluminium AWG 14...AWG 4 copper
Electrical Connection	Lugs
Grounding Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium: busbar
Enclosure Material	Welded sheet steel
Cover Finish	Baked enamel Gray

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Box Number	2
Height	9.29 in (236 mm)
Width	4.80 in (122 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901785149
Nbr. of units in pkg.	1
Package weight(Lbs)	3.81 lb(US) (1.73 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	4.00 in (10.160 cm)
Package 1 width	6.50 in (16.510 cm)
Package 1 Length	11.10 in (28.194 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------