

# Product data sheet

## Characteristics

# QO320GFI

Mini circuit breaker, QO, 20A, 3 pole, 208Y/120 VAC, 10 kA, 6mA grd fault A, pigtail, plug in mount

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	208Y/120 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate

### Complementary

Interrupt Rating	10 kA 208Y/120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m) 0.00...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) AWG 16...AWG 14) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in <sup>2</sup> (4...20 mm <sup>2</sup> ) AWG 12...AWG 4)
Height	4.12 in (104.65 mm)
Width	2.25 in (57.15 mm)
Depth	2.91 in (73.91 mm)

### Environment

Certifications	UL Listed CSA
----------------	------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Rating	104 °F (40 °C)
----------------	----------------

### Ordering and shipping details

Category	00103 - QO 2 POLE GFI CB 40-60A
Discount Schedule	DE2A
GTIN	00785901298588
Nbr. of units in pkg.	15
Package weight(Lbs)	15 lb(US) (6.80 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	2.70 in (6.858 cm)
Package 1 width	3.40 in (8.636 cm)
Package 1 Length	6.50 in (16.510 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

