

Product availability : Stock - Normally stocked in distribution facility



Main

Marketing Trade Name	QO
Product	Load Center
Enclosure Type	Weatherproof enclosure
Cover Type	Surface cover

Complementary

Load Center Type	Main breaker
Rated Current	200 A
Number of Spaces	30
Max Short Circuit Current Rating	25 kA
Maximum Number of Single Pole Circuits	30
Maximum Number of Tandem Breakers	0
Number of Phases	3 phase
Voltage Rating	208Y/120 V AC 240/120 V delta AC 240 V delta AC
Wire Size	AWG 4...300 kcmil aluminium/copper
Electrical Connection	Lugs
Grounding Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Wiring Configuration	3-wire 4-wire
Busbar Material	Tin plated copper busbar
Enclosure Material	Welded galvanized steel
Cover Finish	Baked enamel Gray

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Box Number	14R
Height	39.37 in (1000 mm)
Width	14.76 in (375 mm)

Environment

Enclosure Rating	NEMA 3R outdoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	00017 - QO 3PH LOAD CENTER,OUTDOOR
Discount Schedule	DE3
GTIN	00785901290612
Nbr. of units in pkg.	1
Package weight(Lbs)	47 lb(US) (21.32 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	40.98 in (104.1 cm)
Package 1 width	5.12 in (13 cm)
Package 1 Length	15.39 in (39.1 cm)
Package 2 Weight	1155.00 lb(US) (523.899 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------