

Product data sheet

Characteristics

QO340GFI

Mini circuit breaker, QO, 40A, 3 pole, 208Y/120 VAC, 10 kA, 6mA grd fault A, pigtail, plug in mount

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	40 A
Voltage Rating	208Y/120 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 208Y/120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 12...AWG 4 aluminium AWG 14...AWG 6 copper
Tightening Torque	40.71 lbf.in (4.6 N.m) 0.00...0.02 in ² (2.5...10 mm ²) AWG 16...AWG 14) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in ² (4...20 mm ²) AWG 12...AWG 4)
Height	4.12 in (104.65 mm)
Depth	2.91 in (73.91 mm)
Width	2.25 in (57.15 mm)

Environment

Certifications	UL Listed CSA
----------------	------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Rating	104 °F (40 °C)
----------------	----------------

Ordering and shipping details

Category	00103 - QO 2 POLE GFI CB 40-60A
Discount Schedule	DE2A
GTIN	00785901979043
Package weight(Lbs)	1.41 lb(US) (0.64 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

