

# Product data sheet

## Characteristics

# QO350EPD

Mini circuit breaker, QO, 50A, 3 pole, 240 VAC, 10 kA, 30mA grd fault B, plug in mount

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

|                       |                                       |
|-----------------------|---------------------------------------|
| Product               | Miniature circuit-breaker             |
| Range                 | QO                                    |
| Current Rating        | 50 A                                  |
| Voltage Rating        | 240 V AC                              |
| Mounting Type         | Plug-in                               |
| Number of Poles       | 3P                                    |
| Circuit Breaker Type  | Ground fault protecting class B 30 mA |
| Ratings               | Not rated                             |
| Electrical Connection | Box lugs                              |

### Complementary

|                        |   |
|------------------------|---|
| Interrupt Rating       | 10 kA 240 V AC 50/60 Hz   |
| Number of Panel Spaces | 3   |
| Wire Size              | AWG 12...AWG 4 aluminium<br>AWG 14...AWG 6 copper   |
| Tightening Torque      | 40.71 lbf.in (4.6 N.m) 0.00...0.02 in <sup>2</sup> (2.5...10 mm <sup>2</sup> ) AWG 16...AWG 14)<br>40.71 lbf.in (4.6 N.m) 0.01...0.03 in <sup>2</sup> (4...20 mm <sup>2</sup> ) AWG 12...AWG 4) |
| Height                 | 4.12 in (104.65 mm)   |
| Width                  | 2.25 in (57.15 mm)  |
| Depth                  | 2.91 in (73.91 mm)  |

### Environment

|                |                  |
|----------------|------------------|
| Certifications | UL Listed<br>CSA |
| Ambient Rating | 104 °F (40 °C)   |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 00910 - QO-EPD,QOB-EPD BREAKERS |
| Discount Schedule     | DE2A                            |
| GTIN                  | 00785901957126                  |
| Nbr. of units in pkg. | 15                              |
| Package weight(Lbs)   | 15 lb(US) (6.80 kg)             |
| Returnability         | Yes                             |
| Country of origin     | MX                              |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>             |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End of Life Information</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions

