

Product data sheet

Characteristics

QOB3125VH

Mini circuit breaker, QO, 125A, 3 pole, 120/240 VAC, 22 kA, bolt on mount

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|-----------------------|--------------------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Current Rating | 125 A |
| Voltage Rating | 120/240 V AC 240 V AC 120 V AC |
| Mounting Type | Bolt-on |
| Number of Poles | 3P |
| Circuit Breaker Type | Standard |
| Ratings | Not rated |
| Electrical Connection | Box lugs |

Complementary

| | |
|------------------------|---|
| Interrupt Rating | 22 kA 120/240 V AC 50/60 Hz 22 kA 240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz |
| Number of Panel Spaces | 6 |
| Wire Size | AWG 4...300 kcmil copper or aluminium |
| Tightening Torque | 40.71 lbf.in (4.6 N.m) |
| Height | 5.72 in (145.29 mm) |
| Width | 4.5 in (114.30 mm) |
| Depth | 4.9 in (124.46 mm) |

Environment

| | |
|----------------|------------------|
| Certifications | UL Listed CSA |
|----------------|------------------|

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|----------------|----------------|
| Ambient Rating | 104 °F (40 °C) |
|----------------|----------------|

Ordering and shipping details

| | |
|-----------------------|------------------------------|
| Category | 00015 - QOB CIRCUIT BREAKERS |
| Discount Schedule | DE2 |
| GTIN | 00785901065470 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|-----------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 4.30 in (10.922 cm) |
| Package 1 width | 5.00 in (12.7 cm) |
| Package 1 Length | 6.80 in (17.272 cm) |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 558 |
| Package 2 Weight | 2216.00 lb(US) (1005.16 kg) |
| Package 2 Height | 40.00 in (101.6 cm) |
| Package 2 width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|