

Product data sheet

Characteristics

QOC30UF

Cover, QO, load center, 30 circuits, flush

Product availability : Stock - Normally stocked in distribution facility



Main

Marketing Trade Name	QO
Product	Load Center Cover

Complementary

Cover Type	Flush cover
For Use With	For indoor load center
Surface finish	Painted Gray
Number of circuits	30
Height	31.06 in (788.92 mm)
Width	15.44 in (392.18 mm)
Depth	0.7 in (17.78 mm)
Tightening torque	20.36 lbf.in (2.3 N.m) cover

Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901745952
Package weight(Lbs)	13.4 lb(US) (6.08 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 2 Weight	879.00 lb(US) (398.707 kg)
------------------	----------------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------