

# Product data sheet

## Characteristics

# QOC40UF

## Cover, QO, load center, 40 circuits, flush

Product availability : Stock - Normally stocked in distribution facility



### Main

Marketing Trade Name	QO
Product	Load Center Cover

### Complementary

Cover Type	Flush cover
For Use With	For indoor load center
Surface finish	Painted Gray
Number of circuits	40
Height	34.98 in (888.49 mm)
Width	15.44 in (392.18 mm)
Depth	0.7 in (17.78 mm)
Tightening torque	20.36 lbf.in (2.3 N.m) cover

### Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901745969
Package weight(Lbs)	11.3 lb(US) (5.13 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 2 Weight	998.00 lb(US) (452.685 kg)
------------------	----------------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

**Offer Sustainability**

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

**Contractual warranty**

Warranty	18 months
----------	-----------