

Product data sheet

Characteristics

QOE250GF1NM

Load center, QO, 1 phase, 50A enclosed main breaker, NEMA3R, ground fault protection, nonmetallic, spa

Product availability : Stock - Normally stocked in distribution facility



Main

Marketing Trade Name	QO
Product	Load Center
Enclosure Type	Weatherproof enclosure

Complementary

Load Center Type	Main breaker
Rated Current	50 A
Number of Spaces	2
Max Short Circuit Current Rating	10 kA
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Electrical Connection	Lugs
Grounding Bar	Grounding bar (factory installed)
Wiring Configuration	3-wire
Enclosure Material	Non-metallic
Cover Finish	Baked enamel Gray
Box Number	1NM
Height	9.17 in (233 mm)
Width	6.54 in (166 mm)
Depth	3.90 in (99 mm)

Environment

Enclosure Rating	NEMA 3R outdoor
------------------	-----------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	UL Listed
------------------------	-----------

Ordering and shipping details

Category	00167 - DE3A MISC
Discount Schedule	DE3A
GTIN	00785901389507
Nbr. of units in pkg.	1
Package weight(Lbs)	2.4 lb(US) (1.09 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.00 in (10.16 cm)
Package 1 width	6.80 in (17.272 cm)
Package 1 Length	9.50 in (24.13 cm)
Package 2 Weight	24.90 lb(US) (11.294 kg)
Package 3 Weight	645.00 lb(US) (292.567 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------